

HL-i series compact design makes it highly suitable for weighing applications at work, school, home or anywhere



New Innovative Novel Japanese Apparatus





Clearly a Better Value

L'L'a

Batteries Included

/ High Weighing Resolution of 1/2000

Precision weighing of 200g x 0.1g for HL-200i and 2000g x 1g for HL-2000i

/ Calibration Function

Easy and simple to calibrate the scale with external calibration mass for accurate weighing

Multi Weighing Units

Meet any weighing application with weighing units of g, oz, ct and tael for HL-200i and g, oz, lb-oz and teal for HL-2000i

/ Two Way Power

Use either 4 x AA batteries or the optional AC adapter

/Long Battery Life

Continuous operation for 1000 hours using alkaline batteries

I Tare Function to Full Weighing Capacity

One touch tare using the "RE-ZERO" key enables the user to use a weighing container and still benefit from the full weighing range of the scale!

/Large LCD Display

Easy to read 13.5mm LCD display

/Large Weighing Pan

Easily weigh large objects on the 130mm diameter weighing pan

/Auto Power Off Function

Save battery life with the Auto Power Off function. HL-i automatically shuts down after 5 minutes of disuse

Low Battery Indication

Low battery warning is displayed when the batteries are running low

/ Overload Indication

Display indicator for scale overload conditions

/ Stable Indicator

Lets you know when the scale is stable and ready to weigh ensuring accurate weighing results

/ Compact Size

Small size means it's easy to use anywhere. The scale can also be stored on its side or rear, saving space!



New Innovative Novel Japanese Apparatus

A&D Company, Limited

3-23-14 Higashi-Ikebukuro, Toshima-ku,Tokyo 170-0013 JAPAN Telephone:[81](3) 5391-6132 Fax:[81](3) 5391-6148 http://www.aandd.jp

A&D ENGINEERING, INC.

A&D MERCURY PTY. LTD.

32 Dew Street, Thebarton, South Australia 5031 AUSTRALIA Telephone:[61](8) 8301-8100 Fax:[61](8) 8352-7409

...Clearly a Better Value

A&D INSTRUMENTS LTD. Unit 24/26 Blacklands Way Abingdon Business Park, Abingdon, Oxon OX14 1DY United Kingdom Telephone:[44](1235) 550420 Fax:[44](1235) 550485

<German Sales Office> Große Straße 13 b 22926 Ahrensburg GERMANY Telephone:[49](0) 4102 459230 Fax:[49](0) 4102 459231

A&D KOREA Limited

Manhattan Bldg. 8F, 36-2 Yoido-dong, Youngdeungpo-gu, Seoul, KOREA Telephone:[82](2) 780-4101 Fax:[82](2) 782-4280

HL-i Series Specifications

	HL-200 <i>i</i>	HL-2000 <i>i</i>
Capacity x Resolution	200g x 0.1 g	2000 g x 1 g
	7.05 oz x 0.01 oz	70.5 oz x 0.1 oz
	1000.0 ct x 0.5 ct	4 lb 6.6 oz x 0.1 oz
	5.335 tl x 0.005 tl *	53.35 tl x 0.05 tl *
Non-linearity	±0.2g	± 2g
Repeatability	0.1g	1g
Span drift	±0.015% / °C TYP (5°C~35°C / 41°F~95°F)	
Operating temp.	- 10°C~40°C / 14°F~104°F, Less than 85%RH	
Display	13.5 mm / 0.53 in., 7segment liquid crystal display	
Display update	Approximately 5 times per second	
Power	4 x "AA" size batteries or AC adapter	
Battery life	Approximately 1000 hours with alkaline cells at 20°C / 68°F	
Pan size	130mm / 5.1in.	
Dimensions	130(W)x192(D)x51(H)mm / 5.1(W)x7.6(D)x2.0(H)in.	
Weight	Approximately 500g / 1.1lb	
Calibration weight	200g	2000g
Option	AC adapter	
* the Taiwan tool		

* tl : Taiwan tael

Options

AX-TB-196 AC100V with A plug AX-TB-202 AC120V with A plug AX-TB-164 AC220-230V with C plug AX-TB-173 AC220-230V with BF plug AX-TB-172 AC220-240V with S plug

