

# SJ-HS

*This Stainless Steel Weighing Pan is extremely practical for all kinds of hygienic applications*



*SJ-1000HS SJ-2000HS SJ-5000HS SJ-12KHS*



**AND** ...Clearly a Better Value  
A&D Company, Limited  
<http://www.aandd.jp>

# SJ-HS

Food service, Stores, Post offices, Industries, Factories, Schools, Laboratories, Warehouses, Offices, Home use and a wide range of other diverse weighing applications are possible.

## ■ Stainless steel weighing pan

### ■ High resolution

(SJ-5000HS:1/2500, SJ-12KHS:1/2400, SJ-1000HS/2000HS: 1/2000)

### ■ Fast stability time – Less than 1 second

### ■ Large wide LCD display (25mm height)

### ■ Durable body

### ■ Large weighing pan 230mm x 190mm

### ■ Full digital calibration function

### ■ Multiple weighing units – g, lb, oz and lb-oz

### ■ Battery operation with 4 x D size dry batteries

### ■ Simple and easy to change the batteries

### ■ Optional AC adapter

### ⏻ OFF ➔ Automatic power OFF function

### ■ Spirit level and adjustable feet for accurate weighing

### ■ Status indication function – Battery, Stable, Zero and Net




## SJ-HS Specifications

	SJ-1000HS	SJ-2000HS	SJ-5000HS	SJ-12KHS	
Capacity x Resolution	g	1000g x 0.5g	2000g x 1g	5000g x 2g	12kg x 0.005kg
	lb	2.2lb x 0.001lb	4.4lb x 0.002lb	11lb x 0.005lb	26lb x 0.01lb
	oz	35oz x 0.02oz	70oz x 0.05oz	176oz x 0.1oz	423oz x 0.2oz
	lb-oz	2.2lb x 0.1 oz	4.4lb x 0.1 oz	11lb x 0.1oz	26lb x 1 oz
Linearity	±1g	±2g	±5g	±10g	
Repeatability (S.D.)	1g	2g	5g	10g	
Span drift	±0.015% / °C TYP ( 5°C~35°C/ 41°F~95°F)				
Display	Liquid Crystal Display , 25mm / 0.98 inches				
Operating temperature	-10°C~40°C / 14°F~104°F, less than 85% RH (No condensation)				
Display update	Approx. 10 times per second				
Power	4 x R20P / LR20 / "D" size batteries or AC adapter				
Battery life	Approx. 800 hours with alkaline cells at 20°C / 68°F				
Pan size	230 (W) x 190 (D) mm / 9.05 (W) x 7.48 (D) inches				
Dimensions	265 (W) x 250 (D) x 103 (H) mm / 10.4 (W) x 9.8 (D) x 4.1 (H) inches				
Weight	Approx. 2.1kg / 4.6lb				
Calibration mass	1000g	2000g	5000g	10kg	

Specifications subject to change for improvement without notice

## External Dimensions (mm / inches)



## Accessories

<b>AX-TB164B</b>	AC adapter	AC 230V "C" type plug
<b>AX-TB173A</b>	AC adapter	AC 230V "BF" plug
<b>AX-TB196</b>	AC adapter	AC 100 "A" type plug
<b>AX-TB202</b>	AC adapter	AC 120 "A" type plug

# A&D

...Clearly a Better Value

### A&D Company, Limited

3-23-14 Higashi-Ikebukuro, Toshima-ku, Tokyo 170-0013 JAPAN  
Telephone:[81](3) 5391-6132 Fax:[81](3) 5391-6148  
http://www.aandd.jp

### A&D ENGINEERING, INC.

1555 McCandless Drive, Milpitas, CA. 95035 U.S.A.  
Telephone:[1](408) 263-5333 Fax:[1](408) 263-0119

### A&D MERCURY PTY. LTD.

32 Dew Street, Thebarton, South Australia 5031 AUSTRALIA  
Telephone:[61](8) 8301-8100 Fax:[61](8) 8352-7409

### A&D INSTRUMENTS LTD.

Unit 24/26 Blacklands Way Abingdon Business Park,  
Abingdon, Oxon OX14 1DY United Kingdom  
Telephone:[44](1235) 550420 Fax:[44](1235) 550485

### <German Sales Office>

Große Straße 13 b 22926 Ahrensburg GERMANY  
Telephone:[49](0) 4102 459230 Fax:[49](0) 4102 459231

### A&D KOREA Limited

Manhattan Bldg. 8F, 36-2 Yoido-dong, Youngdeungpo-gu, Seoul, KOREA  
Telephone:[82](2) 780-4101 Fax:[82](2) 782-4280

### A&D RUS CO. LTD.

Korp.134A, D.29, UL. Vereiskaya, Moscow, 121357  
RUSSIAN FEDERATION  
Telephone: [7] (495) 727-4455 Fax: [7] (495) 727-4456